



BGSSE228430TP-H-US1

by CMC

Catalog ID: BGSSE228430TP-H-US1

Solar Cabinet, Exterior dimensions: 22" deep x 84" wide x 30" high.

- Strut design utilized for easy junction hanging
- Heavy-Duty channelized construction
- Fabricated from 12 gauge galvaneel steel
- Also available in mild steel, aluminum, or stainless steel (contact rep)
- Heavy duty wind locks are standard
- Stainless steel hinge barrels, pins, padlock hasp, and exterior hardware
- Full 3/8" diameter solid copper ground loop standard
- Oven cured green powder coat polyester finish exceeds ANSI standard C57.12.28
- Standard paint color: Munsell dark green. Provides a safe and convenient primary cable terminating, sectionalizing, tapping, and switching point for underground solar distribution systems

Optional predrilled 18" mating fiberglass sleeve (BFGBS228418-PD) available, "sold separately".

Product Details

General

Material	Steel, Galvannealed
UPC	192663134595

Dimensions

Cubic Capacity	55440 cu.in
Depth	22 in
Height	30 in
Width	84 in



CONNECTOR MANUFACTURING COMPANY
3501 Symmes Road
Hamilton, Ohio 45015 - 1369
513 - 860 - 4455(Press 2 for Customer Service and Sales)
To email customer Service: [jrex @cmclugs.com](mailto:jrex@cmclugs.com)

