



BMAC-162

by CMC

Catalog ID: BMAC-162

Banded transformer cluster mounts, mounts 2 KVA thru 50 KVA Transformers

- Made with high strength extruded 6061-T6 aluminum alloy
- With ground wire clamp (supplied standard)
- Ultimate load 6,000# total 2,000# per position
- 12" NEMA transformer spacing
- EE1-NEMA type A lugs
- Completely assembled with hardware
- Extension kit available by adding "-5 to BMAC XXXX"
- Mounts one transformer 6" from pole

Product Details

General

Type	Bolted Pole Mount Bracket
------	---------------------------