



BN4080604SS

by Wiegmann
Catalog ID: BN4080604SS

N4X JIC Lift-Off Cover 8X6X4 304 Stainless Steel

- Bodies and doors fabricated from 16 gauge type 304 stainless steel. Continuously welded seams ground smooth, less knockouts or holes. Sealed with poured-in-place polyurethane gasket. External mounting plates, top and bottom of enclosure. Weldnuts are provided to secure optional panel. Stainless steel screws and clamps on four sides of cover assure watertight seal. Grounding provisions provided. Optional panels and terminal kits must be ordered separately.

Product Details

General

| | |
|-------------------------|---|
| Application | Provides unmatched protection for housing electrical components in highly corrosive environments. This enclosure is used in indoor and outdoor settings that are frequently wet or have constant exposure to water, other liquids, or contaminants. |
| Construction | Continuously Welded Seams |
| Cover Type | Lift Off |
| Knockouts | No |
| Latches Type | Clamps |
| Listings | UL, CSA |
| Material | 304 Stainless Steel |
| Mounting Type | Wall Mount |
| Number of Doors (Fixed) | 1 |
| Series | BN4-SS |
| Type | Enclosure |
| UPC | 786725378913 |

Dimensions

| | |
|----------------|-----------|
| Cubic Capacity | 192 cu.in |
| Depth | 4 in |
| Height | 8 in |
| Weight | 4 lb |

| | |
|-------|------|
| Width | 6 in |
|-------|------|

Certifications and Compliance

| | |
|------------------|--|
| Certified Listed | <ul style="list-style-type: none">• CSA• IEC• UL |
| Nema Rating | 4X |
| UL Listed | Yes |