



BN4121005SS

by Wiegmann
Catalog ID: BN4121005SS

N4X JIC Lift-Off Cover 12X10X5 304 Stainless Steel

- Bodies and doors fabricated from 16 gauge type 304 stainless steel. Continuously welded seams ground smooth, less knockouts or holes. Sealed with poured-in-place polyurethane gasket. External mounting plates, top and bottom of enclosure. Weldnuts are provided to secure optional panel. Stainless steel screws and clamps on four sides of cover assure watertight seal. Grounding provisions provided. Optional panels and terminal kits must be ordered separately.

Product Details

General

Application	Provides unmatched protection for housing electrical components in highly corrosive environments. This enclosure is used in indoor and outdoor settings that are frequently wet or have constant exposure to water, other liquids, or contaminants.
Construction	Continuously Welded Seams
Cover Type	Lift Off
Knockouts	No
Latches Type	Clamps
Listings	UL, CSA
Material	304 Stainless Steel
Mounting Type	Wall Mount
Number of Doors (Fixed)	1
Series	BN4-SS
Type	Enclosure
UPC	786725378951

Dimensions

Cubic Capacity	600 cu.in
Depth	5 in
Height	12 in
Weight	12 lb

Width	10 in
-------	-------

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">• CSA• IEC• UL
Nema Rating	4X
UL Listed	Yes