



127556, XL Shear Bolt WEJTAP™ Connector

By Burndy

Catalog # [127556](#)



Main Conductor: 1351.5 AAC - 1351.5 ACSR (1.340"-1.386") Tap
Conductor: 556.5 ACSR (24/7 Str) - 715.5 ACSR (.914"-1.036")

Features

- Industry-proven spring wedge technology easily installed with common socket or impact wrench - No Special Tools Required!
- "Spring Like" high strength C-Body ensures permanent connection with consistent pressure on the conductors
- Meets or exceeds current carrying capacity of conductors being connected
- Corrosion resistant highly conductive aluminum alloys with a pure aluminum insert between conductors increases conductivity and lowers electrical resistance
- Corrosion inhibitor factory applied for ease of installation
- Remains permanently locked through fault current or power surges
- Easy to remove without damage to conductor

- May be used in non-corrosive environments to connect copper conductors
- Excellent option for emergency storm restoration

General

Catalog Number 127556

Conductor Related

Conductor Range Main Conductor: 1351.1 AAC-1351.5 ACSR, Tap: 556.5-715.5 ACSR

Product Assets

[Excel Files - Burndy-CPI WEJTAP Connector Selector](#)
[Installation Manuals - Tap Connector Installation Instructions](#)
[Specifications - 127556](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
BRDY-127556-SPEC-EN | REV 3/2025