



1PBS750HD, UV Rated Black Splice Reducer, 2-sided 2-port, 750-6

By Burndy
Catalog # [1PBS750HD](#)



750-6 TWO-SIDED 2 PORT HD BLK.

Features

- UV Rated Covering over AL6061-T6 aluminum body saves time, lowering installation costs and eliminates taping
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces the number of connectors necessary to carry in inventory

General

Catalog Number	1PBS750HD
Connector Type	Multi Tap
Hex Key	3/8
Installation Torque Recommended in-lb	500 in-lb
Insulation	Y
Insulation Type	Plastisol
Material	Aluminum
Material - Hardware	Aluminum
Number Of Ports	4
Physical Attribute - Number of Screws	4
Temperature Rating	-40°C to 135°C
Trade Name	UNITAP™
UPC	621945480810

Dimensions

Dimension - Height inch	3.01
Dimension - L Length Overall mm	267
Dimension - Length Overall inch	10.53

Electrical Ratings

Amperage Rating	535 A
Voltage - Maximum	600 V

Conductor Related

Conductor - Copper Str Size Range	6 AWG - 750 kcmil
Conductor Size	2 AWG-750 KCMIL

Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section A - Mechanical](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50079816](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-1PBS750HD-SPEC-EN | REV 6/2024