



1PL2/02, UV Rated Black, 1-sided, 2-port, #14-2/0 AWG

By Burndy
Catalog # 1PL2/02



Aluminum Multiple Tap Connector, UV Rated, 2 Port, 1 Sided Entry, 14-2/0 AWG.

Features

- UV Rated Covering over AL6061-T6 aluminum body saves time, lowering installation costs and eliminates taping
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces the number of connectors necessary to carry in inventory

Application

For Indoor Use Only, Copper Or Stranded Aluminum

General

Catalog Number	1PL2/02
Connector Type	Multi Tap
EU RoHS Indicator	Yes
Hex Key	3/16
Installation Torque Recommended in-lb	120
Insulation	Y
Insulation Type	Plastisol
Material	Aluminum
Material - Hardware	Aluminum
Number Of Ports	2
Physical Attribute - Number of Screws	2
Plated	N
Plating Type	Unplated
Sub Brand	UNITAP
Temperature Rating	194° F
Trade Name	UNITAP™
Type	BIBS, Multi-Port
UPC	781810287484
UPC 12 Digit	7818102874844

Dimensions

Dimension - Height fraction	1.375 in
Dimension - Height inch	1.38 in
Dimension - L Length Overall mm	39 mm
Dimension - Length Overall inch	1.52 in
Dimension - Screw Size inch	1/4
Dimension - Width fraction	1-2/5 in
Dimension - Width inch	1.40 in
Dimension - Width mm	36 mm

Electrical Ratings

Voltage - Maximum 600 V

Conductor Related

Conductor - AL Str Size	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG
Conductor - AL Str Size Range	14 AWG - 2/0 AWG
Conductor - Copper Str Size	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG
Conductor - Copper Str Size Range	14 AWG - 2/0 AWG
Conductor Size	14-2/0 AWG
Conductor Type	<ul style="list-style-type: none">• AL C Str-Size• CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity 1

Product Assets

[3D Models - 1PL202_MODEL-IGES](#)
[3D Models - 1PL202_MODEL-STEP](#)
[3D Models - 1PL202_MODEL-PDF](#)
[Catalogs - Section A - Mechanical](#)
[Catalogs - UNITAP™ Products](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_1PL202_LineArt](#)
[Sales Drawings - SD214514-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-1PL202-SPEC-EN | REV 6/2024