



1PLD75010HD, UV Rated Black, 2-sided, 10-port, #2 AWG-750 kcmil

By Burndy
Catalog # [1PLD75010HD](#)



750-2 TWO-SIDED 10 PORT HD BLK.

Features

- UV Rated Covering over AL6061-T6 aluminum body saves time, lowering installation costs and eliminates taping
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces the number of connectors necessary to carry in inventory

General

Catalog Number	1PLD75010HD
Connector Type	Multi Tap
Hex Key	3/8 in
Installation Torque	500
Recommended in-lb	
Insulation	Y
Material	Aluminum
Number Of Ports	10
Temperature Rating	-40°C to 135°C
Trade Name	UNITAP™
UPC	621945480797

Dimensions

Dimension - L Length Overall	346.202
mm	
Dimension - Length Overall	13.63
inch	

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor Size	2 AWG-750 KCMIL
----------------	-----------------

Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section A - Mechanical](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50079815](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-IPLD75010HD-SPEC-EN | REV 6/2024