



1PLD75012HD, UV Rated Black, 2-sided, 12-port, #2 AWG-750 kcmil

By Burndy
Catalog # [1PLD75012HD](#)



750-2 TWO-SIDED 12 PORT HD BLK.

Features

- UV Rated Covering over AL6061-T6 aluminum body saves time, lowering installation costs and eliminates taping
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces the number of connectors necessary to carry in inventory

General

Catalog Number	1PLD75012HD
Connector Type	Multi Tap
Hex Key	3/8 in
Installation Torque Recommended in-lb	500 in-lb
Insulation	Y
Material	Aluminum
Number Of Ports	12
Temperature Rating	-40°C to 135°C
Trade Name	UNITAP™
UPC	621945480803

Dimensions

Dimension - L Length Overall mm	416.052
Dimension - Length Overall inch	16.38

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor Size	2 AWG-750 KCMIL
----------------	-----------------

Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section A - Mechanical](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50079815](#)



A proud member of the Hubbell Family.