



1PLD7502HD, UV Rated Black, 2-sided, 2-port, #2 AWG-750 kcmil

By Burndy
Catalog # [1PLD7502HD](#)



750-2 TWO-SIDED 2 PORT HD BLK.

Features

- UV Rated Covering over AL6061-T6 aluminum body saves time, lowering installation costs and eliminates taping
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces the number of connectors necessary to carry in inventory

General

Catalog Number	1PLD7502HD
Connector Type	Multi Tap
Hex Key	3/8 in
Installation Torque Recommended in-lb	500 in-lb
Material	Aluminum
Number Of Ports	2
Temperature Rating	-40°C to 135°C
Trade Name	UNITAP™
UPC	621945480728

Dimensions

Dimension - L Length Overall mm	66.802
Dimension - Length Overall inch	2.63

Electrical Ratings

Voltage - Maximum 600 V

Conductor Related

Conductor Size 2 AWG-750 KCMIL

Certifications And Compliance

Certification - CSA Approved No
Standards - RoHS Compliance CM
Status
UL Listed Yes

Logistics

Minimum Pack Quantity 1

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section A - Mechanical](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50079815](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-1PLD7502HD-SPEC-EN | REV 6/2024