



# 1PLD7503HD, UV Rated Black, 2-sided, 3-port, #2 AWG-750 kcmil

By Burndy  
Catalog # [1PLD7503HD](#)



750-2 TWO-SIDED 3 PORT HD BLK.

## General

Connector Type	UV Rated Black UNITAP
Hex Key	3/8 in
Installation Torque Recommended in-lb	500 in-lb
Material	Aluminum
Number Of Ports	3
Temperature Rating	-40°C to 135°C
Trade Name	UNITAP™
UPC	621945480735

## Dimensions

Dimension - L Length Overall mm	101.6
Dimension - Length Overall inch	4

## Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

## Conductor Related

Conductor Size	2 AWG-750 KCMIL
----------------	-----------------

## Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - 50079815](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-1PLD7503HD-SPEC-EN | REV 1/2024