



1PLD7504HD, UV Rated Black, 2-sided, 4-port, #2 AWG-750 kcmil

By Burndy
Catalog # 1PLD7504HD



750-2 TWO-SIDED 4 PORT HD BLK.

Features

- UV Rated Covering over AL6061-T6 aluminum body saves time, lowering installation costs and eliminates taping
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces the number of connectors necessary to carry in inventory

General

Catalog Number	1PLD7504HD
Connector Type	Multi Tap
Hex Key	3/8 in
Installation Torque Recommended in-lb	500 in-lb
Material	Aluminum
Number Of Ports	4
Temperature Rating	-40°C to 135°C
Trade Name	UNITAP™
UPC	621945480742

Dimensions

Dimension - L Length Overall mm	136.652
Dimension - Length Overall inch	5.38

Electrical Ratings

Voltage - Maximum 600 V

Conductor Related

Conductor Size 2 AWG-750 KCMIL

Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Minimum Pack Quantity 1

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50079815](#)
- [Specifications - 1PLD7504HD](#)



A Hubbell brand