

1PLD7505HD, UV Rated Black, 2-sided, 5-port, #2 AWG-750 kcmil

By Burndy
Catalog # 1PLD7505HD



750-2 TWO-SIDED 5 PORT HD BLK.

Features

- UV Rated Covering over AL6061-T6 aluminum body saves time, lowering installation costs and eliminates taping
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces the number of connectors necessary to carry in inventory

General

Catalog Number	1PLD7505HD
Connector Type	Multi Tap
Hex Key	3/8 in
Installation Torque	500 in-lb
Recommended in-lb	
Material	Aluminum
Number Of Ports	5
Temperature Rating	-40°C to 135°C
Trade Name	UNITAP™
UPC	621945480766

Dimensions

Dimension - L Length Overall mm	171.45
Dimension - Length Overall inch	6.75

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor Size	2 AWG-750 KCMIL
----------------	-----------------

Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50079815](#)
- [Specifications - 1PLD7505HD](#)