



# 1PLD7506HD, UV Rated Black, 2-sided, 6-port, #2 AWG-750 kcmil

By Burndy  
Catalog # 1PLD7506HD



750-2 TWO-SIDED 6 PORT HD BLK.

## Features

- UV Rated Covering over AL6061-T6 aluminum body saves time, lowering installation costs and eliminates taping
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces the number of connectors necessary to carry in inventory

## General

Catalog Number	1PLD7506HD
Connector Type	Multi Tap
Hex Key	3/8 in
Installation Torque Recommended in-lb	500 in-lb
Material	Aluminum
Number Of Ports	6
Temperature Rating	-40°C to 135°C
Trade Name	UNITAP™
UPC	621945480773

## Dimensions

Dimension - L Length Overall mm	206.502
Dimension - Length Overall inch	8.13

## Electrical Ratings

Voltage - Maximum 600 V

## Conductor Related

Conductor Size 2 AWG-750 KCMIL

## Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

## Logistics

Minimum Pack Quantity 1

## Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50079815](#)  
[Specifications - 1PLD7506HD](#)