



1PLD7508HD, UV Rated Black, 2-sided, 8-port, #2 AWG-750 kcmil

By Burndy
Catalog # [1PLD7508HD](#)

750-2 TWO-SIDED 8 PORT HD BLK.



General

Connector Type	UV Rated Black UNITAP
Hex Key	3/8 in
Installation Torque Recommended in-lb	500 in-lb
Material	Aluminum
Number Of Ports	8
Temperature Rating	-40°C to 135°C
Trade Name	UNITAP™
UPC	621945480780

Dimensions

Dimension - L Length Overall mm	276.352
Dimension - Length Overall inch	10.88

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor Size	2 AWG-750 KCMIL
----------------	-----------------

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50079815](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-1PLD7508HD-SPEC-EN | REV 1/2024