


1PLMD2/06, UV Rated Black, Mount Tap, 2-sided, 6-port

By Burndy
Catalog # [1PLMD2/06](#)



Mounted Block Tap Connector, Single Side Entry, 5.29 IN L.

Features

- UV Rated Covering over AL6061-T6 aluminum body saves time, lowering installation costs and eliminates taping
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces the number of connectors necessary to carry in inventory

General

Connector Type	Multi Tap
Installation Torque Recommended in-lb	120 in-lb
Insulation	Y
Insulation Type	Plastisol
Material	Aluminum
Material - Hardware	Aluminum
Number Of Ports	6
Physical Attribute - Number of Screws	8
Plated	Y
Plating Type	Clear Plated
Temperature Rating	194° F
Trade Name	UNITAP™
UPC	781810307533
UPC 12 Digit	7818103075333

Dimensions

Dimension - Height fraction	1-1/2 in
Dimension - Height inch	1.5
Dimension - L Length Overall mm	134
Dimension - Length Overall inch	5.29
Dimension - Width inch	1.56
Dimension - Width mm	40 mm

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - AL Str Size	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG
Conductor - AL Str Size Range	14 AWG - 2/0 AWG
Conductor - Copper Str Size	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG
Conductor - Copper Str Size Range	14 AWG - 2/0 AWG
Conductor Size	14-2/0 AWG
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Size • CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - UNITAP™ Products](#)
[Product Cross Section Image\(s\) - BUR_PLM_LineArt](#)
[Sales Drawings - 50015715](#)

