



Die Set, #22 AWG - #10 AWG Nylon and Vinyl, Terminals and Splices, Interchangeable for PAT221 Crimper

By Burndy
Catalog # [2210NV221](#)

Die Set, #22 AWG - #10 AWG Nylon and Vinyl, Terminals and Splices, use with PAT221 Crimper

Features

- Accommodates copper connector sizes: #22 AWG - #10 AWG Nylon and Vinyl Insulated
- Easy groove identification with color coded dies
- UL Listed connections when used with recommended BURNDY terminals/splices

Application

Crimping

General

Application - For Use On	Copper Terminals, Splices
Catalog Number	2210NV221
Die Type	Interchangeable
Type	Die
UPC	621945666160
UPC 12 Digit	621945666160

Dimensions



Weight 0.1 lb

Conductor Related

Crimping Ranges Copper: #22 AWG - #10 AWG nylon and vinyl, terminals and splices

Certifications And Compliance

Buy American Compliant No

Logistics

Package Contents Die Set Only

Product Assets

[Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - Sales Drawing 50124041](#)