



## 25CHENET, 1/4" Silicon Bronze Hex Nut, Tin Plated

By Burndy  
Catalog # 25CHENET



Electro Tin Plated Silicon Bronze 1/4-20 Nut.

### General

Connector Type	Nut
Installation Torque	80 LBS/in
Recommended in-lb	
Material	SILICON BRONZE
Trade Name	DURIUM™
UPC	781810120606
UPC 12 Digit	7818101206066

### Dimensions

Dimension - Bolt Size fraction	1/4
Dimension - Bolt Size inch	0.25 in
Dimension - Outside Diameter inch	0.44 in
Dimension - Thread Size	1/4 - 20
Dimension - Threads per inch	20

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	50
Minimum Pack Quantity	50

### Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - 50059117](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-25CHENET-SPEC-EN | REV 1/2024