

25X300HEBBOX, 1/4" x 3" Hex Bolt, Silicon Bronze

By Burndy
Catalog # [25X300HEBBOX](#)

Silicon Bronze Hexagonal Head Bolt, 3.00 IN L, 1/4 IN-20 Thread Size.



Features

- DURIUM™ silicon bronze hardware combines high strength and corrosion resistance
- Silicon bronze per ASTM B99

General

Catalog Number	25X300HEBBOX
Connector Type	Bolt - Hex
Installation Torque	80 LBS/in
Recommended in-lb	
Material	SILICON BRONZE
Trade Name	DURIUM™
UPC	781810011331
UPC 12 Digit	7818100113311

Dimensions

Dimension - B Length fraction	3 in
Dimension - B Length inch	3 in
Dimension - Bolt Size fraction	1/4
Dimension - Bolt Size inch	0.25 in
Dimension - Length Overall inch	3 in
Dimension - Thread Size	1/4 - 20

Dimension - Threads per inch 20

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	50
Minimum Pack Quantity	10
Pallet Quantity	48000

Product Assets

[Catalogs - BURNDY Master Catalog - Section F - Accessories](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_HEBBOX_LineArt1](#)
[Sales Drawings - 50037908](#)
[Specifications - 25X300HEBBOX](#)