



25X300HEBET, 1/4" x 3" Hex Bolt, Silicon Bronze, Tin Plated

By Burndy
Catalog # [25X300HEBET](#)



Electro Tin Plated Silicon Bronze Hexagonal Head Bolt, 3.00 IN L, 1/4 IN-20 Thread Size.

General

Connector Type	Bolt - Hex
Installation Torque	80 LBS/in
Recommended in-lb	
Material	SILICON BRONZE
UPC	781810249222
UPC 12 Digit	781810249222

Dimensions

Dimension - B Length fraction	3 in
Dimension - B Length inch	3 in
Dimension - Bolt Size fraction	1/4
Dimension - Bolt Size inch	0.25 in
Dimension - Thread Size	1/4 - 20
Dimension - Threads per inch	20

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	500
Minimum Pack Quantity	500
Pallet Quantity	58000

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-25X300HEBET-SPEC-EN | REV 1/2024