



25X75HEBET, 1/4" x 3/4" Hex Bolt, Silicon Bronze, Tin Plated

By Burndy
Catalog # [25X75HEBET](#)



Electro Tin Plated Silicon Bronze Bolt, 1/4-20 IN Thread, Stud
Length: 3/4 IN, Hexagonal Head.

General

Connector Type	Bolt - Hex
Installation Torque	80 LBS/in
Recommended in-lb	
Material	SILICON BRONZE
UPC	781810114339
UPC 12 Digit	7818101143399

Dimensions

Dimension - B Length fraction	3/4 in
Dimension - B Length inch	0.75 in
Dimension - Bolt Size fraction	1/4
Dimension - Bolt Size inch	0.25 in
Dimension - Thread Size	1/4 - 20
Dimension - Threads per inch	20

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100
Minimum Pack Quantity	100
Pallet Quantity	29600

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-25X75HEBET-SPEC-EN | REV 1/2024