

31X125HEBET, 5/16" x 1-1/4" Hex Bolt, Silicon Bronze, Tin Plated

By Burndy
Catalog # 31X125HEBET



5/16 x 1.25 Electro Tin Plate Bolt.

Features

- Tin Plated DURIUM™ silicon bronze hardware combines high strength and corrosion resistance
- Silicon bronze per ASTM B99

General

Catalog Number	31X125HEBET
Connector Type	Bolt - Hex
Installation Torque	180 LBS/in
Recommended in-lb	
Material	SILICON BRONZE
Trade Name	DURIUM™
UPC	781810256114
UPC 12 Digit	7818102561144

Dimensions

Dimension - B Length fraction	1-1/4 in
Dimension - B Length inch	1.25 in
Dimension - Bolt Size fraction	5/16
Dimension - Bolt Size inch	0.3125 in
Dimension - Thread Size	5/16-18

Dimension - Threads per inch 18

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	500
Minimum Pack Quantity	500
Pallet Quantity	99999

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_HEBBOX_LineArt1](#)
[Specifications - 31X125HEBET](#)