



38CHENBOX100, 3/8" Hex Nut, Silicon Bronze

By Burndy
Catalog # 38CHENBOX100



Silicon Bronze NUT ,3/8-16 Stud ,Thread series-Class 2B.

General

Catalog Number	38CHENBOX100
Connector Type	Nut
Installation Torque	180 LBS/in
Recommended in-lb	
Material	SILICON BRONZE
UPC	781810376133

Dimensions

Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.375 in
Dimension - Outside Diameter inch	0.56 in
Dimension - Thread Size	3/8-16
Dimension - Threads per inch	16

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	1
Minimum Pack Quantity	1

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_38CHENBOX_LineArt](#)
- [Sales Drawings - wsc206494-01](#)
- [Specifications - 38CHENBOX100](#)