



38X100HSSBUSA, 3/8" x 1" Hex Bolt, Stainless Steel

By Burndy

Catalog # [38X100HSSBUSA](#)

3/8 x 1.00 Stainless Steel Bolt.



Features

- Stainless Steel hardware is manufactured from 18-8 non-magnetic material
- Nut surfaces and bolt heads have American National Coarse Series, Class #2 fit

General

Catalog Number	38X100HSSBUSA
Connector Type	Bolt - Hex
Installation Torque	240 LBS/in
Recommended in-lb	
Material	STAINLESS STEEL
UPC	781810330302
UPC 12 Digit	7818103303022

Dimensions

Dimension - B Length fraction	1 in
Dimension - B Length inch	1 in
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.38 in
Dimension - Thread Size	3/8-16

Dimension - Threads per inch 16

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100
Minimum Pack Quantity	1

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_HEBBOX_LineArt1](#)
- [Sales Drawings - 50052495](#)
- [Specifications - 38X100HSSBUSA](#)