

38X150HEBBOX, 3/8" x 1-1/2" Hex Bolt, Silicon Bronze

By Burndy
Catalog # [38X150HEBBOX](#)



Silicon Bronze Bolt, 1.50 in L, Hexagonal bolts.

Features

- DURIMUM™ silicon bronze hardware combines high strength and corrosion resistance
- Silicon bronze per ASTM B99

Application

For Use On Outdoor Connector Applications

General

Catalog Number	38X150HEBBOX
Connector Type	Bolt - Hex
EU RoHS Indicator	Yes
Installation Torque	240 LBS/in
Recommended in-lb	
Material	SILICON BRONZE
Sub Brand	DURIMUM
Trade Name	DURIMUM™
Type	Bolt
UPC	781810011744
UPC 12 Digit	7818100117444

Dimensions

Dimension - B Length fraction	1-1/2 in
Dimension - B Length inch	1.5 in
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.375 in

Dimension - Length Overall	1.50 in
Dimension - Thread Size	3/8-16
Dimension - Threads per inch	16

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	1000
Minimum Pack Quantity	1
Pallet Quantity	96000

Product Assets

[Catalogs - BURNDY Master Catalog - Section F - Accessories](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_HEBBOX_LineArt1](#)
[Sales Drawings - 50037908](#)
[Specifications - 38X150HEBBOX](#)