



38X150HEBET, 3/8" x 1-1/2" Hex Bolt, Silicon Bronze, Tin Plated

By Burndy
Catalog # [38X150HEBET](#)



3/8 x 1.50 Electro Tin Plated Bolt.

General

Connector Type	Bolt - Hex
Installation Torque Recommended in-lb	240 LBS/in
Material	SILICON BRONZE
Trade Name	DURIUM™
UPC	781810158920
UPC 12 Digit	7818101589200

Dimensions

Dimension - B Length fraction	1-1/2 in
Dimension - B Length inch	1.5 in
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.375 in
Dimension - Thread Size	3/8-16
Dimension - Threads per inch	16

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	500
Minimum Pack Quantity	1
Pallet Quantity	30000

Product Assets

- [3D Models - 38X150HEBET_MODEL-PDF](#)
- [3D Models - 38X150HEBET_MODEL-IGES](#)
- [3D Models - 38X150HEBET_MODEL-STEP](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Product Cross Section Image\(s\) - BUR_HEBBOX_LineArt1](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-38X150HEBET-SPEC-EN | REV 5/2024