



## 38X150OSBBOX, 3/8" x 1-1/2" Oval Shank Bolt

By Burndy  
Catalog # [38X150OSBBOX](#)



3/8 x 1.50 Oval Shank Bolt.

### General

Connector Type	Bolt - Oval Shank
Installation Torque	240 LBS/in
Recommended in-lb	
Material	SILICON BRONZE
UPC	781810362020
UPC 12 Digit	7818103620200

### Dimensions

Dimension - B Length fraction	1-1/2 in
Dimension - B Length inch	1.5 in
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.375 in
Dimension - Thread Size	3/8-16
Dimension - Threads per inch	16

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_HEBBOX\\_LineArt1](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-38X150OSBBOX-SPEC-EN | REV 6/2024