



38X175HEBET, 3/8" x 1-3/4" Hex Bolt, Silicon Bronze, Tin Plated



By Burndy

Catalog # 38X175HEBET

3/8 x 1.75 Electro Tin Plated Bolt.

Features

- Tin Plated DURIMUM™ silicon bronze hardware combines high strength and corrosion resistance
- Silicon bronze per ASTM B99

General

Catalog Number	38X175HEBET
Connector Type	Bolt - Hex
Installation Torque	240 LBS/in
Recommended in-lb	
Material	SILICON BRONZE
Trade Name	DURIMUM™
UPC	781810463451
UPC 12 Digit	7818104634511

Dimensions

Dimension - B Length fraction	1-3/4 in
Dimension - B Length inch	1.75 in
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.375 in
Dimension - Thread Size	3/8-16
Dimension - Threads per inch	16

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Minimum Pack Quantity	250
-----------------------	-----

Product Assets

- [3D Models - 38X175HEBET_MODEL-IGES](#)
- [3D Models - 38X175HEBET_MODEL-STEP](#)
- [3D Models - 38X175HEBET_MODEL-PDF](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_HEBBOX_LineArt1](#)
- [Specifications - 38X175HEBET](#)



A Hubbell brand