



38X175OSBBOX, 3/8" x 1-3/4" Oval Shank Bolt

By Burndy
Catalog # [38X175OSBBOX](#)



3/8 x 1.75 Oval Shank Bolt.

General

Connector Type	Bolt - Oval Shank
Installation Torque	240 LBS/in
Recommended in-lb	
Material	SILICON BRONZE
UPC	781810362037
UPC 12 Digit	7818103620377

Dimensions

Dimension - B Length fraction	1-3/4 in
Dimension - B Length inch	1.75 in
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.375 in
Dimension - Thread Size	3/8-16
Dimension - Threads per inch	16

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_HEBBOX_LineArt1](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-38X175OSBBOX-SPEC-EN | REV 5/2024