



38X225HEBET, 3/8" x 2-1/4" Hex Bolt, Silicon Bronze, Tin Plated



By Burndy
Catalog # [38X225HEBET](#)

3/8 x 2.25 Electro Tin Plated Bolt.

General

Catalog Number	38X225HEBET
Connector Type	Bolt - Hex
Installation Torque	240 LBS/in
Recommended in-lb	
Material	SILICON BRONZE
Trade Name	DURIUM™
UPC	781810463093
UPC 12 Digit	7818104630933

Dimensions

Dimension - B Length fraction	2-1/4 in
Dimension - B Length inch	2.25 in
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.375 in
Dimension - Thread Size	3/8-16
Dimension - Threads per inch	16

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Minimum Pack Quantity	200
-----------------------	-----

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_HEBBOX_LineArt1](#)
- [Specifications - 38X225HEBET](#)