



## 38X225OSBBOX, 3/8" x 2-1/4" Oval Shank Bolt

By Burndy

Catalog # [38X225OSBBOX](#)

3/8 x 2.25 Oval Shank Bolt.



### Features

- Prevents Rotation
- Increased Stability
- Reduces wear and tear on the hole and bolt
- Improved load distribution and specified application fit

### General

|                     |                   |
|---------------------|-------------------|
| Catalog Number      | 38X225OSBBOX      |
| Connector Type      | Bolt - Oval Shank |
| Installation Torque | 240 LBS/in        |
| Recommended in-lb   |                   |
| Material            | SILICON BRONZE    |
| UPC                 | 781810362013      |
| UPC 12 Digit        | 7818103620133     |

### Dimensions

|                                |          |
|--------------------------------|----------|
| Dimension - B Length fraction  | 2-1/4 in |
| Dimension - B Length inch      | 2.25 in  |
| Dimension - Bolt Size fraction | 3/8      |
| Dimension - Bolt Size inch     | 0.375 in |

Dimension - Thread Size 3/8-16

Dimension - Threads per inch 16

### Certifications And Compliance

|                               |    |
|-------------------------------|----|
| Certification - CSA Approved  | No |
| Certification - ETL           | No |
| Certification - UL Recognized | No |
| Certification - cULus         | No |
| Standards - RoHS Compliance   | CM |
| Status                        |    |
| UL Listed                     | No |

### Logistics

Minimum Pack Quantity 1

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

[Customer Notices - Prop 65 Notice](#)

[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)

[Product Cross Section Image\(s\) - BUR\\_HEBBOX\\_LineArt1](#)

[Specifications - 38X225OSBBOX](#)



A Hubbell brand