



## 38X225OSBBOX, 3/8" x 2-1/4" Oval Shank Bolt

By Burndy

Catalog # [38X225OSBBOX](#)

3/8 x 2.25 Oval Shank Bolt.



### General

Catalog Number	38X225OSBBOX
Connector Type	Bolt - Oval Shank
Installation Torque	240 LBS/in
Recommended in-lb	
Material	SILICON BRONZE
UPC	781810362013
UPC 12 Digit	7818103620133

### Dimensions

Dimension - B Length fraction	2-1/4 in
Dimension - B Length inch	2.25 in
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.375 in
Dimension - Thread Size	3/8-16
Dimension - Threads per inch	16

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_HEBBOX\\_LineArt1](#)
- [Specifications - 38X225OSBBOX](#)



A Hubbell brand