



38X325HEBBOX, 3/8" x 3-1/4" Hex Bolt, Silicon Bronze

By Burndy

Catalog # [38X325HEBBOX](#)

Silicon Bronze Hexagonal Head Bolt, 3.25 IN L, 3/8 IN-16 Thread Size.

Features

- DURIUM™ silicon bronze hardware combines high strength and corrosion resistance
- Silicon bronze per ASTM B99

General

Catalog Number	38X325HEBBOX
Connector Type	Bolt - Hex
Installation Torque	240 LBS/in
Recommended in-lb	
Material	SILICON BRONZE
Trade Name	DURIUM™
UPC	781810011539
UPC 12 Digit	7818100115399

Dimensions

Dimension - B Length fraction	3-1/4 in
Dimension - B Length inch	3.25 in
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.38 in
Dimension - Length Overall inch	3.25 in
Dimension - Thread Size	3/8-16



Dimension - Threads per inch 16

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	50
Minimum Pack Quantity	1
Pallet Quantity	19200

Product Assets

- [Catalogs - BURNDY Master Catalog - Section F - Accessories](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_HEBBOX_LineArt1](#)
- [Sales Drawings - 50037908](#)
- [Specifications - 38X325HEBBOX](#)