



## 38X75HEBET, 3/8" x 3/4" Hex Bolt, Silicon Bronze, Tin Plated

By Burndy  
Catalog # [38X75HEBET](#)



3/8 x .75 Electro Tin Plated Bolt.

### General

Connector Type	Bolt - Hex
Installation Torque	240 LBS/in
Recommended in-lb	
Material	SILICON BRONZE
Trade Name	DURIUM™
UPC	781810142998
UPC 12 Digit	7818101429988

### Dimensions

Dimension - B Length fraction	3/4 in
Dimension - B Length inch	0.75 in
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.375 in
Dimension - Thread Size	3/8-16
Dimension - Threads per inch	16

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	500
-----------------------	-----

### Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-38X75HEBET-SPEC-EN | REV 1/2024