

## 50CHENBOX, 1/2" Hex Nut, Silicon Bronze

By Burndy  
Catalog # 50CHENBOX



Silicon Bronze NUT ,1/2 Stud ,Thread series-Class 28.

### Application

Used to fasten the joints

### General

Catalog Number	50CHENBOX
Connector Type	Nut
EU RoHS Indicator	Yes
Installation Torque	480 LBS/in
Recommended in-lb	
Material	SILICON BRONZE
Sub Brand	DURIUM
Trade Name	DURIUM™
Type	HARDWARE
UPC	781810012406
UPC 12 Digit	7818100124066

### Dimensions

Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5 in
Dimension - Outside Diameter inch	0.75 in
Dimension - Thread Size	1/2-13
Dimension - Threads per inch	13

### Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	50
Minimum Pack Quantity	1
Pallet Quantity	48000

### Product Assets

- [3D Models - 50CHENBOX\\_MODEL-STEP](#)
- [3D Models - 50CHENBOX\\_MODEL-IGES](#)
- [3D Models - 50CHENBOX\\_MODEL-PDF](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section F - Accessories](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_38CHENBOX\\_LineArt](#)
- [Sales Drawings - wsc206494-01](#)
- [Specifications - 50CHENBOX](#)