

## 50X125HEBET, 1/2" x 1-1/4" Hex Bolt, Silicon Bronze, Tin Plated

By Burndy  
Catalog # 50X125HEBET



1/2 x 1.25 Electro Tin Plated Hex Bolt.

### Features

- Tin Plated DURIMUM™ silicon bronze hardware combines high strength and corrosion resistance
- Silicon bronze per ASTM B99

### General

Catalog Number	50X125HEBET
Connector Type	Bolt - Hex
Installation Torque	480 LBS/in
Recommended in-lb	
Material	SILICON BRONZE
Trade Name	DURIMUM™
UPC	781810109298
UPC 12 Digit	7818101092988

### Dimensions

Dimension - B Length fraction	1-1/4 in
Dimension - B Length inch	1.25 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5 in
Dimension - Thread Size	1/2-13

Dimension - Threads per inch 13

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

### Logistics

Carton Quantity	200
Minimum Pack Quantity	200
Pallet Quantity	14800

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_HEBBOX\\_LineArt1](#)  
[Specifications - 50X125HEBET](#)