



## 50X150HSSBUSA, 1/2" x 1-1/2" Hex Bolt, Stainless Steel

By Burndy

Catalog # [50X150HSSBUSA](#)

Stainless Steel Hexagonal Head Bolt, 1-1/2 IN L, 1/2 IN-13 Thread Size.

### Features

- Stainless Steel hardware is manufactured from 18-8 non-magnetic material
- Nut surfaces and bolt heads have American National Coarse Series, Class #2 fit

### General

Catalog Number	50X150HSSBUSA
Connector Type	Bolt - Hex
Installation Torque	480 LBS/in
Recommended in-lb	
Material	STAINLESS STEEL
UPC	781810330333
UPC 12 Digit	7818103303333

### Dimensions

Dimension - B Length fraction	1-1/2 in
Dimension - B Length inch	1.5 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5 in
Dimension - Thread Size	1/2-13



Dimension - Threads per inch 13

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

### Logistics

Carton Quantity	100
Minimum Pack Quantity	1
Pallet Quantity	46400

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_HEBBOX\\_LineArt1](#)
- [Specifications - 50X150HSSBUSA](#)