

50X200HEBBOX, 1/2" x 2" Hex Bolt, Silicon Bronze



By Burndy
Catalog # 50X200HEBBOX

Silicon Bronze Bolt, 2 in L, Thread Series Class-2A.

Features

- DURIMUM™ silicon bronze hardware combines high strength and corrosion resistance
- Silicon bronze per ASTM B99

Application

For Use On Outdoor Connector Applications

General

Catalog Number	50X200HEBBOX
Connector Type	Bolt - Hex
EU RoHS Indicator	Yes
Installation Torque	480 LBS/in
Recommended in-lb	
Material	SILICON BRONZE
Sub Brand	DURIMUM
Trade Name	DURIMUM™
Type	Bolt
UPC	781810011782
UPC 12 Digit	7818100117822

Dimensions

Dimension - B Length fraction	2 in
Dimension - B Length inch	2 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5 in

Dimension - Length Overall	2 in
inch	
Dimension - Thread Size	1/2-13
Dimension - Threads per inch	13

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	50
Minimum Pack Quantity	1
Pallet Quantity	9600

Product Assets

- [Catalogs - BURNDY Master Catalog - Section F - Accessories](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_HEBBOX_LineArt1](#)
- [Sales Drawings - 50037908](#)
- [Specifications - 50X200HEBBOX](#)