



50X200HSSBBOX, 1/2" x 2" Hex Bolt, Stainless Steel



By Burndy
Catalog # [50X200HSSBBOX](#)

Stainless Steel Bolt, Stud Length: 2 IN,Hexagonal Head.

Application

For Use On Outdoor Connector Applications

General

Catalog Number	50X200HSSBBOX
Connector Type	Bolt - Hex
Construction Material - Main	Stainless Steel
EU RoHS Indicator	Contact Manufacturer
Installation Torque	480 LBS/in
Recommended in-lb	
Material	Stainless Steel
Sub Brand	HARDWARE BOLT
Type	HSSB,Hexagonal Bolts
UPC	781810361146
UPC 12 Digit	7818103611466

Dimensions

Dimension - B Length fraction	2 in
Dimension - B Length inch	2 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5 in
Dimension - Thread Size	1/2-13
Dimension - Threads per inch	13
Dimensions	0.5 in x 13 in x 2 in
Height	2 in
Length	0.5 in
Width	13 in

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certification - CSA Approved	No
Standards - RoHS Compliance	CM
Status	

Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	14400

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section F - Accessories](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_HEBBOX_LineArt1](#)
[Specifications - 50X200HSSBBOX](#)