



50X225HEBET, 1/2" x 2-1/4" Hex Bolt, Silicon Bronze, Tin Plated

By Burndy
Catalog # 50X225HEBET



1/2 x 2.25 Electro Tin Plate Hex Bolt.

Features

- Tin Plated DURIMUM™ silicon bronze hardware combines high strength and corrosion resistance
- Silicon bronze per ASTM B99

General

Catalog Number	50X225HEBET
Connector Type	Bolt - Hex
Installation Torque	480 LBS/in
Recommended in-lb	
Material	SILICON BRONZE
UPC	781810218372
UPC 12 Digit	7818102183722

Dimensions

Dimension - B Length fraction	2-1/4 in
Dimension - B Length inch	2.25 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5 in
Dimension - Thread Size	1/2-13

Dimension - Threads per inch 13

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Minimum Pack Quantity 100

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_HEBBOX_LineArt1](#)
[Specifications - 50X225HEBET](#)