



50X250HSSBBOX, 1/2" x 250" Hex Bolt, Stainless Steel

By Burndy
Catalog # [50X250HSSBBOX](#)

Stainless Steel Hexagonal Head Bolt, 2.50 IN L, 1/2 IN-13 Thread Size.



Application

For Use On Outdoor Connector Applications

General

Catalog Number	50X250HSSBBOX
Connector Type	Bolt - Hex
EU RoHS Indicator	Yes
Installation Torque	480 LBS/in
Recommended in-lb	
Material	Stainless Steel
Sub Brand	HARDWARE BOLT
Type	HSSB,Hexagonal Bolts
UPC	781810361535
UPC 12 Digit	7818103615355

Dimensions

Dimension - B Length fraction	2-1/2 in
Dimension - B Length inch	2.5 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5 in
Dimension - Thread Size	1/2-13
Dimension - Threads per inch	13

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	1000
Minimum Pack Quantity	1
Pallet Quantity	58000

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section F - Accessories](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_HEBBOX_LineArt1](#)
- [Sales Drawings - 50041364](#)
- [Specifications - 50X250HSSBBOX](#)