

## 50X300HSSBBOX, 1/2" x 3" Hex Bolt, Stainless Steel

By Burndy

Catalog # [50X300HSSBBOX](#)



Stainless Steel Bolt, 3 in L, Thread Size: 1/2-13 in.

### Features

- Stainless Steel hardware is manufactured from 18-8 non-magnetic material
- Nut surfaces and bolt heads have American National Coarse Series, Class #2 fit

### Application

For Use On Outdoor Connector Applications

### General

Catalog Number	50X300HSSBBOX
Connector Type	Bolt - Hex
EU RoHS Indicator	Yes
Installation Torque	480 LBS/in
Recommended in-lb	
Material	STAINLESS STEEL
Sub Brand	STAINLESS STEEL HARDWARE
Type	Bolt
UPC	781810361153
UPC 12 Digit	78181036115

### Dimensions

Dimension - B Length fraction	3 in
Dimension - B Length inch	3 in
Dimension - Bolt Size fraction	1/2

Dimension - Bolt Size inch	0.5 in
Dimension - Thread Size	1/2-13
Dimension - Threads per inch	13

### Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

### Logistics

Carton Quantity	100
Minimum Pack Quantity	1
Pallet Quantity	11100

### Product Assets

[Catalogs - BURNDY Master Catalog - Section F - Accessories](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_HEBBOX\\_LineArt1](#)  
[Specifications - 50X300HSSBBOX](#)