



50X300OSBBOX, 1/2" x 3" Oval Shank Bolt

By Burndy
Catalog # [50X300OSBBOX](#)



1/2 x 3.00 Oval Shank Bolt.

General

Connector Type	Bolt - Oval Shank
Installation Torque Recommended in-lb	480 LBS/in
Material	STAINLESS STEEL
UPC	781810462010
UPC 12 Digit	7818104620100

Dimensions

Dimension - B Length fraction	3 in
Dimension - B Length inch	3 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5 in
Dimension - Thread Size	1/2-13
Dimension - Threads per inch	13

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Product Cross Section Image\(s\) - BUR_HEBBOX_LineArt1](#)



A proud member of the Hubbell Family.