



50X325HABBOX, 1/2" x 3-1/4" Hex Bolt, Aluminum

By Burndy
Catalog # 50X325HABBOX



Al Hexagon Head Bolt, 2-1/4 IN L, 1/2 IN-13 Thread Size.

Features

Aluminum hardware finished with anodic coating

General

Catalog Number	50X325HABBOX
Connector Type	Bolt - Hex
Installation Torque	480 LBS/in
Recommended in-lb	
Material	ALUMINUM
UPC	781810012161
UPC 12 Digit	7818100121611

Dimensions

Dimension - B Length fraction	2-1/4 in
Dimension - B Length inch	2.25 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5 in
Dimension - Length Overall inch	2.25 in
Dimension - Thread Size	1/2-13
Dimension - Threads per inch	13

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	50
Minimum Pack Quantity	50
Pallet Quantity	19600

Product Assets

- [Catalogs - BURNDY Master Catalog - Section F - Accessories](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_HABBOX_LineArt](#)
- [Sales Drawings - 50041363](#)
- [Specifications - 50X325HABBOX](#)