



## 62X175HG5B, 5/8" x 1-3/4" Hex Bolt, Galvanized Steel

By Burndy  
Catalog # 62X175HG5B



5/8 x 1.75 Galvanized Steel Hex Bolt.

### Features

- Galvanized steel hardware (bolts, nuts, flatwashers and internal tooth lockwashers) are manufactured per ASTM307 Grade A
- Nut surfaces and bolt heads have American Standard dimensions
- Galvanizing is per ASTM A153

### General

Catalog Number	62X175HG5B
Material	GALVANIZED STEEL
UPC	781810435397

### Dimensions

Dimension - B Length fraction	1-3/4 in
Dimension - B Length inch	1.75 in
Dimension - Bolt Size fraction	5/8
Dimension - Bolt Size inch	0.625 in
Dimension - Length Overall inch	1.75 in

Dimension - Thread Size 5/8-11

Dimension - Threads per inch 11

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	NC
Status	
UL Listed	No

### Logistics

Minimum Pack Quantity 1

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Specifications - 62X175HG5B](#)