

## ACC-FPV90, Stainless Steel, 90 degree, 2 wire Module Cable Clip

By Burndy  
Catalog # ACC-FPV90



2 wire Module Cable Clip 90 Degree

### Features

- Accommodates a broad range of cable combinations and sizes
- Environmentally tested (UL2703 and ASTM B117)
- No tools required for installation
- Coined and rolled edges to prevent damage to cable insulation

### Application

1 to 2 PV cables, Wire Diameter Range: 5.0mm - 8.0mm per each cable

### General

Catalog Number	ACC-FPV90
Construction Material - Main	304 STAINLESS STEEL
EU RoHS Indicator	Under Review
Material	304 Stainless Steel
Mounting Method	Module Frame or Flange Clip - 90 Degree, Flange Thickness Range: 1.0mm - 3.0mm
Sub Brand	Clip
Type	Cable clip
UPC	621945514508

### Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certification - CSA Approved	Yes
Certification - cULus	Yes
Certified Listed	UL1565
Industry Standard(s)	UL1565
UL Listed	Yes

### Logistics

Minimum Pack Quantity	1000
-----------------------	------

### Product Assets

[Catalogs - BURNDY Master Catalog - Section E4 - Wiley Grounding](#)  
[Catalogs - Wiley Wire Management Guide](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)  
[Certifications - UL Certificate of Compliance, UL 1565, CSA C22.2 No. 18.5-13](#)  
[Sales Drawings - 50084791](#)  
[Specifications - Burndy\\_ACC-FPV90\\_Specsheet](#)  
[Specifications - ACC-FPV90](#)  
[Video - Wiley 90 Degree Module Clips](#)