



ASA1000U, Terminal Stacking Adaptor, Al/Cu, 1000 kcmil

By Burndy
Catalog # [ASA1000U](#)



Terminal Stacking Adaptor, 1000 kcmil, UL Listed 90 Deg C,600 Volts to 35 kV.

Features

- For use on terminals made from copper or aluminum
- May be used with standard NEMA two and four hole terminals
- TO stack four hole NEMA terminations use two stacking adaptors assembled side-by-side
- Only three sizes necessary to accommodate terminals from 250 kcmil through 1000 kcmil

Application

For Aluminum And Copper Terminals

General

Catalog Number	ASA1000U
EU RoHS Indicator	Yes
Installation Torque	480 LBS/in
Recommended in-lb	
Material	Aluminum
Material - Hardware	DURIUM™ Silicon Bronze
Physical Attribute - Number of Holes	2
Physical Attribute - Number of Screws	2
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	Y
Plating Type	Tin
Sub Brand	HYSTACK
Temperature Rating	194° F
Trade Name	HYSTACK™
Type	Stacking Adapters
UPC	781810521045
UPC 12 Digit	7818105210455

Dimensions

Dimension - Bolt Size inch	3.75 in
Dimension - Height fraction	1-1/4 in
Dimension - Height inch	1.25 in
Dimension - Height mm	31.8 mm
Dimension - L Length Overall mm	23 mm
Dimension - Length Overall inch	0.91 in
Dimension - Pad Width inch	1.25 in

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - AL Str Size	1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil;397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil;550 kcmil;556 kcmil;600 kcmil;636 kcmil;650 kcmil;700 kcmil;715 kcmil;750 kcmil;795 kcmil;800 kcmil;874 kcmil;900 kcmil;954 kcmil;1000 kcmil
Conductor - AL Str Size Range	1/0 AWG-1000 kcmil
Conductor - Copper Str Size	1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil;800 kcmil;850 kcmil;900 kcmil;1000 kcmil
Conductor - Copper Str Size Range	1/0 -1000 kcmil
Conductor Type	• AL C Str-Size • CU C Str-Size

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	4640

Product Assets

[3D Models - ASA1000U_MODEL-PDF](#)

[3D Models - ASA1000U_MODEL-IGES](#)

[3D Models - ASA1000U_MODEL-STEP](#)

[Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

[Customer Notices - Prop 65 Notice](#)

[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)

[Product Cross Section Image\(s\) - BUR_ASA-U_LineArt](#)

[Sales Drawings - sd078073-01](#)

[Specifications - ASA1000U](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-ASA1000U-SPEC-EN | REV 10/2024