



B21D20D25CG1 Flexible Copper Braid

By Burndy
Catalog # [B21D20D25CG1](#)

Flexible Copper Braid, 262 kcmil, U - Shape.



General

Catalog Number	B21D20D25CG1
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	2
Plated	Y
UPC	781810460382
UPC 12 Digit	7818104603822

Dimensions

Dimension - L Length Overall mm	514 mm
Dimension - Length Overall inch	20.25 in
Length	20.25 in

Electrical Ratings

Rating - Indoor Amperage	304
Rating - Outdoor Amperage	364

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	12
Minimum Pack Quantity	1
Pallet Quantity	864

Product Assets

- [3D Models - B21D20D25CG1_MODEL-PDF](#)
- [3D Models - B21D20D25CG1_MODEL-STEP](#)
- [3D Models - B21D20D25CG1_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 10080994](#)
- [Specifications - B21D20D25CG1](#)