



B22E124N Flexible Copper Braid

By Burndy
Catalog # [B22E124N](#)

Flexible Copper Braid.



General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	4
Plated	N
UPC	781810511183
UPC 12 Digit	7818105111833

Dimensions

Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	305 mm
Dimension - Length Overall inch	12.00 in
Length	12 in

Electrical Ratings

Rating - Outdoor Amperage	800 A
---------------------------	-------

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Carton Quantity	4
Minimum Pack Quantity	1
Pallet Quantity	360

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 30020726](#)



A proud member of the Hubbell Family.