

## B22E184N Flexible Copper Braid

By Burndy  
Catalog # B22E184N

Flexible Copper Braid.



### Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: [www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

### General

Catalog Number	B22E184N
Connector Type	Braid
Material	Copper
Physical Attribute - Number of Braids	4
UPC	781810042175
UPC 12 Digit	7818100421755

### Dimensions

Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	457 mm

Dimension - Length Overall inch	18 in
Length	18 in

### Electrical Ratings

Rating - Outdoor Amperage	800 A
---------------------------	-------

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	4
Minimum Pack Quantity	1
Pallet Quantity	360

### Product Assets

- [3D Models - B22E184N\\_MODEL-IGES](#)
- [3D Models - B22E184N\\_MODEL-PDF](#)
- [3D Models - B22E184N\\_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 30020726](#)
- [Specifications - B22E184N](#)